

DIMENSION	MEASURE		DIMENSION	MEASURE	
APPLIANCE			Indicates whether a protection tray against heat or contact is needed with oven. Default is "N"	No	
Product width	590	mm	Indicates whether a ventilation opening in the back side of cabinet is needed or not with oven. Default is "Y"	Yes	
Product depth	510	mm	Indicates the position of the opening in the back side of the cabinet with oven	Top	
Radius of product corner	10	mm	MIN Width of rear opening required with oven	550	mm
Product height (MAX protrusion from the worktop)	4	mm	MIN Depth of rear opening required with oven.	45	mm
Underneath the bearing area of the appliance	50	mm	MIN AREA of rear opening required with oven	247.5	cm ²
Distance between cut out and top frontal projection	15	mm	MIN distance from cabinet to rear wall, with oven	20	mm
Distance between cut out and top lateral projection	15	mm	Indicates whether a ventilation opening in the top front side of cabinet is needed or not with oven. Default is "N"	No	
Plateau thickness	4	mm	MIN Frontal gap required, with oven (2)	0	mm
Gas outlet positioning	N/A		MIN frontal opening area required with oven	0	cm ²
Gas outlet X positioning	0	mm	WITH CABINET		
Gas outlet Y positioning	0	mm	MIN worktop thickness with cabinet	12	mm
Power cable	With product		MAX worktop thickness with cabinet	0	mm
Power cable positioning	Rear left		Indicates whether a protection tray against heat or contact is needed. Default is "Y"	Yes	
CUT OUT			MIN distance from bottom line of appliance to protection tray	10	mm
MIN front distance from cut-out to end worktop	0	mm	Indicates whether a ventilation opening in the tray is needed or not with cabinet	Yes	
MIN rear distance from cut out to wall/furniture	35	mm	Recess dimension X	90	mm
MIN lateral distance from cut out to wall/furniture	100	mm	Recess dimension Y	120	mm
MIN height from worktop to above furniture	400	mm	Positioning dimension X by axis	45	mm
MIN cut out width	560	mm	Distance of the tray from the back panel/wall	60	mm
MAX cut out width	562	mm	Indicates whether a divider is available	Service accessory	
MIN cut out depth	480	mm	Indicates whether a ventilation opening in the back side of cabinet is needed or not. Default is "Y"	Yes	
MAX cut out depth	492	mm	Indicates the position of the opening in the back side of the cabinet.	Top	
MIN cut out radius	0	mm	MIN Width of rear opening of the cabinet	550	mm
MAX cut out radius	10	mm	MIN Depth of rear opening of the cabinet	45	mm
FLUSH INSTALLATION			MIN AREA of rear opening of the cabinet	247.5	cm ²
Indicates whether a flush installation is possible. Default is "N"	Yes		MIN distance from cabinet to rear wall	20	mm
MIN Milling rabbet width	593	mm	Indicates whether a ventilation opening in the top front side of cabinet is needed or not. Default is "N"	No	
MAX Milling rabbet width	595	mm	MIN Frontal gap of the cabinet	0	mm
MIN Milling rabbet depth	513	mm	MIN frontal opening area of the cabinet	0	cm ²
MAX Milling rabbet depth	515	mm	INSTALLATION SPACE		
Milling rabbet thickness	6	mm	Depth of immersion underneath the appliance	0	mm
Radius milling rabbet	11.5	mm	Width protruding area below bottom box	0	mm
Flush installation KIT (2)	Service KIT		Depth protruding area below bottom box	0	mm
Indicates the minum worktop thickness with standard installation for gas	0	mm	Protruding area: X positioning	0	mm
Indicates the maximum worktop thickness with standard installation for gas	0	mm	Protruding area: Y positioning	0	mm
Indicates the minum worktop thickness with flush installation for gas	0	mm	ACCESSORIES FOR INSTALLATION		
Indicates the maximum worktop thickness with flush installation for gas	0	mm	Gasket	Pre assembled	
WITH OVEN					
Indicates whether the cooktop can be installed above oven. Default is "Y"	Yes				
MIN worktop thickness with oven	28	mm			
MAX worktop thickness with oven	0	mm			

DIMENSION**MEASURE**

Clips	Separate KIT	
Injector KIT	N/A	
Elbow KIT	N/A	
COOKTOP HOOD INSTALLATION ONLY FOR GAS		
MIN distance from cooktop to above furniture	0	mm
MIN distance between cabinets above the cooktop	0	mm
MAX distance between cabinets above the cooktop	0	mm